Point Master 5.x X-Ray CT Image Processing / 3D Measurement Powerful 3D Software for Reverse Engineering





released!!

- **New!** Processing 3D images, point clouds, polygons and CAD data in a single software.
 - Seamlessly working multiple functions including healing, surfacing and shape comparison.
 - Support new functions including defect detection, thickness evaluation and 3D measurement.

Various functions of PointMaster 5

CAD Link



X-ray CT ańd 3D measurements 3D images. measured polygons (STL), point cloud data


PointMaster 5

IGES, data STEP files


3D CAD software (SolidWorks, NX I-deas, Pro/ENGINEER, CATIA etc.)

The CAD Link function offers an easy way to use 3D measurements data in various other fields including CAD, CAM and CAE. It allows users to construct surfaces on a polygon data or approximate it to a combination of shapes such as a plate or cylinder, with the resultant data provided as IGES or STEP files to be used in 3D CAD software.

A volume rendering of X-ray CT images of a battery using CT Module



Shape Comparison




Position and align two different

data sets for comparison, for

example, between CAD data

and measured data, or between

New! 3D Measurement



CAD-like 3D measurement based on 3D measurement data.

New!






Automatically extract defects and particles existing inside the 3D images of casts and resin products. The extracted defects are presented in different colors.

New!





Export STL files for 3D printers

Detect the areas of a specified thickness and display them in different colors.Useful in evaluating the shape based on thickness.



System Requirements

two measured data sets.

- Multiprocessors/multi-core processors supported
- OpenGL 2.0 compatible graphics card with dedicated GPU and VRAM such as NVIDIA Geforce and Quadro series recommended
- All editions of Windows Vista and Windows 7 supported (64-bit versions)
- ◆ The amount of memory recommended to be several times the data size to be processed.
- ◆ 3 million polygons/20 million point clouds can be loaded per GB memory

- ◆ Data volume of a 3D image stack is calculated in the following way:
 - 16bit×512×512pixels×512 slices =256MB $16bit \times 1024 \times 1024 pixels \times 500 slices = 1GB$
- Maximum data size depends on the amount of memory installed.
- ◆ The handling of data whose total size exceeds 1GB requires, large memory (e.g., 8 ~ 32GB).
- Offer 64-bit version of PointMaster only.



Product Lineup

- Basic functions (handling of polygons and point clouds data, reporting)
- ◆ CAD Link
- (surfacing for CAD data generation, shape approximation) CT module

(visualization and processing of 3D images such as CT images)

♦ Shape comparison (position and align two 3D objects for comparison)





About reverse engineering

Reverse engineering using 3D data of real objects obtained through X-ray CT devices or 3D scanners has been actively practiced in recent years. Reverse engineering, in a broader definition, is a process of gathering information on product structure by dissembling the products, obserbing their operation, or analyzing software, in order to investigate their production methods, principles of operation, plans (drawing) and source code. Reverse engineering in the manufacturing industry is generally understood as a way to utilize digital measurement data in other technologies such as CAD, CAE and rapid prototyping for various purposes including design, manufacture and inspection.

* Specification and release time may change without notice. Company and product name are registration of trademark.



ww.nvs.co.ip/ info@nvs.co.ip Coral Bldg. 4F, 6-26-2 Shinjuku, Shinjuku-ku, Tokyo 160-0022, JAPAN TEL: +81-3-5155-5561 FAX:+81-3-5155-5560